

## 6 ft USB to Parallel Printer Adapter - M/M

StarTech ID: ICUSB1284



The ICUSB1284 USB to Parallel Interface Converter Cable allows PCs that support the USB specification to print to any standard parallel printer. The USB interface provides a much faster data transfer rate than a standard parallel port, thereby reducing the time waiting for a print job to be sent to your printer.

This portable device is self-powered and provides Plug and Play installation to any USB-compliant computer running Windows 98/ME/2000/XP/Vista.

### Applications and Solutions

- Allows you to quickly add a parallel port to your Windows 98SE/ME/2000/XP/Vista/Windows 7 computer

## Features

- Fully Plug & Play for easy installation
- Low power consumption as it draws power from the USB connection
- Supports Windows 98SE/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)
- High speed bi-directional parallel port compliant to IEEE-1284 industry standard
- No IRQ required for installation

## Technical Specifications

- Warranty: 1 Year warranty
- Connector Types: 1 - USB A Male
- Connector Types: 1 - Centronics 36 Male
- Product Length: 6.08 ft [1.85 m]
- Power Consumption: .90
- Carton Quantity: 50
- Shipping (Package) Weight: 0.33 lb [0.15 kg]
- Connectors: USB Type A Male, Centronics 36 Male
- Cable Length: 180cm (72 in.)
- Power Consumption: 90mA (max)
- Power Mode: Bus powered
- Enclosure: Plastic
- Weight: 110g
- Certifications: FCC Part 15, CE Mark
- Humidity: 0~80% RH non-condensing
- Operating Temperature: 5°C to 40°C (41°F to 140°F)
- Storage Temperature: -20°C to 70°C (-4°F to 158°F)

