

2 Port ExpressCard RS232 Serial Adapter Card with 16950 UART

StarTech ID: EC2S950



This 2 Port ExpressCard Serial Adapter Card lets you add two serial ports to your laptop or ExpressCard equipped desktop computer, using an available ExpressCard slot.

Featuring 128-byte FIFO communication, and a high performance 16C950 UART, the ExpressCard Serial Adapter card offers up to 921.6Kbps data transfer rates, which ensures peak communication with your serial peripheral devices.

Applications

- Works with serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters, and more.

Features

- Offers 2 DB9 RS-232 ports to connect a serial device to a notebook with an available ExpressCard slot
- 128-byte deep FIFO data buffer
- Maximum data transfer rate up to 921.6 kbps
- Automated in-band flow control

Technical Specifications

Warranty	Lifetime
Ports	2
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Port Style	Dongle (Included)
Chipset ID	PLX/Oxford - OX16PCI954
Connector Type(s)	1 - ExpressCard (34mm)
External Ports	2 - DB-9 (9 pin; D-Sub) Male
Maximum Data Transfer Rate	921.6 Kbps
Serial Protocol	RS-232
OS Compatibility	Windows® 7 (32/64bit), Vista(32/64), XP(32/64), 2000, NT 4.0, ME, 98se Windows® Server 2008, 2008 R2, 2003(32/64) Linux
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - Serial ExpressCard
Included in Package	1 - 2 Port DB9 Adapter Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

