

Features

- 2 years warranty
- ATX version 2.03 & ATX12V compliant
- High quality connectors provide minimal resistance and enhanced electric conductivity
- High-Flow fan provides efficient cooling for the system and power supply
- Provides a maximum output power of 145 Watts
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.
- Superior EMI/RFI power filtration system provides super clean and stable power to all system components

Technical Specifications

- Warranty: 2 Year warranty
- Air Flow Rate: 32.3
- Connector Types: 3 - LP4 Female Large Internal Power
- Connector Types: 1 - SP4 Female Small Internal Power
- Connector Types: 1 - ATX 20 pin Female ATX Motherboard Adapter
- Fan Bearing Type: Sleeve Bearing
- Product Height: 3.35 in [8.5 cm]
- Input Voltage: 115~230
- Input Voltage Frequency: 50~60 Hz
- Product Length: 5.12 in [13 cm]
- MTBF: 40,000
- Noise Level: 27.4
- Fans: 1 - 80 mm
- Current -12.0V (A): 0.3
- Current +12.0V1 (A): 5.5
- Current +3.3V (A): 8
- Current +5.0V (A): 14
- Current +5.0Vsb (A): 1.0
- Output Power: 145
- Power Factor Correction: No
- Carton Quantity: 10
- Shipping (Package) Weight: 2.61 lb [1.18 kg]

- Product Weight: 1.89 lb [0.85 kg]
- Product Width: 3.94 in [10 cm]
- Humidity: 5~90% RH
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Storage Temperature: -20°C to 80°C (-4°F to 176°F)

