

MP3 AirLink

Wireless MP3 Audio Transmitter and Receiver

MP3AUDIOEXT

Instruction Manual



Actual product may vary from photo

StarTech.com

The Professionals' Source for Hard-to-Find Computer Parts

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction	1
Before You Begin	1
Installation	2
Specifications	3
Technical Support	4
Warranty Information	4

Introduction

Thank you for purchasing a StarTech.com Wireless MP3 Audio Transmitter and Receiver. If you want to use your computer, iPod, or MP3 player with your home stereo or speaker system, the MP3AUDIOEXT is the perfect way to do it without worrying about wiring. Using a simple wireless Transmitter and Receiver, you can connect your speakers, portable stereo, receiver, or amplifier to any audio source that uses a standard 3.5mm audio headphone jack. With a small footprint and no software to configure, this product is easy to setup and won't intrude on your workspace.

Features

- Connects an audio source to one or more receivers wirelessly
- 8 selectable wireless channels for excellent clarity
- Easy setup: no software to install or configure
- Small footprint uses a minimal amount of space

Before You Begin

System Requirements

- A MP3 player, iPod, computer, or other audio source with a 3.5mm headphone "audio out" jack
- Speakers, amplifier, receiver, stereo or other audio device

Contents

This package should contain:

- 1 x Transmitter
- 1 x Receiver
- 2 x Power supplies
- 1 x 3.5mm to 3.5mm audio cable
- 1 x 3.5mm to RCA audio cable

Installation

1. Connect one end of the 3.5mm to 3.5mm audio cable to the speaker output of your MP3 player, iPod, computer, or other audio source. Connect the other end of the cable to the "AUDIO IN" jack on the Transmitter.
2. Connect one of the power supplies to the Transmitter and plug it into an electrical outlet or other suitable power source.
3. Connect the two RCA ends of the 3.5mm to RCA audio cable to an unused pair of inputs on your stereo amplifier, speakers, receiver, portable stereo, or other audio output device. Connect the other end of the cable to the "AUDIO OUT" jack on the Receiver.
4. Connect one of the power supplies to the Receiver and plug it into an electrical outlet or other suitable power source.
5. Adjust the output volume of your audio device to about 50%. Start playback of the song(s) you want to hear.
6. Set your audio output device to the audio input you connected the Receiver to. You should hear the music being played from your computer.
7. If needed, press the button on the top of the Transmitter to change broadcast channels for better sound quality. There are 8 channels.

Note: This device operates at a frequency of 2400 ~ 2483.5 MHz, which may conflict with nearby cordless phones or wireless routers running at similar frequencies. To avoid signal interference between the two devices, change broadcast signals on the MP3Airlink accordingly. Failing this, please refer to the documentation included with your cordless phone or wireless router for information on how to change the channel frequency on your wireless router or cordless phone.

Specifications

Feature	Transmitter	Receiver
Supply voltage	3.6 ~ 5 V DC	3.6 ~ 5 V DC
Current consumption	100 mA (typical)	130 mA (typical)
Operating temperature	14 ~ 140 deg. F. (-10 ~ 60 deg. C.)	14 ~ 140 deg. F. (-10 ~ 60 deg. C.)
Frequency range	2400 ~ 2483.5 MHz	2400 ~ 2483.5 MHz
Modulation	FSK (Modulation index 0.5)	
Number of channels	8	8
Channel spacing	9 MHz	9 MHz
Channel frequency	2410, 2419 ~ 2473 MHz	2410, 2419 ~ 2473 MHz
Frequency stability	+/- 100 KHz	+/- 100 KHz
Transmit power	+10 dBm for CE (typical) 0 dBm for FCC (typical)	
Input impedance	>10K Ohm	
Input level	4Vp-p (max)	
Receive sensitivity		-85 dBm (min.)
Adjacent channel rejection		>45dB @ +/- 5 MHz offset the channel frequency
Image rejection		>25dB @ the image frequency
Output impedance		< 1 KOhm
Output level		3.4Vp-p (max)
Response	20 ~ 20 KHz, -1dB	
Dynamic range	92db (typical)	
Separation	80dB (typical)	
S/N ratio	87dB (typical)	
THD	0.1% (typical)	
Power supply	Input: AC 120V @ 60HZ Output: DC 9V, 200 mA (tip is center positive)	

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a one-year warranty. In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product.

Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

About StarTech.com

StarTech.com is “The Professionals’ Source for Hard-to-Find Computer Parts”. Since 1985, we have been providing IT professionals with the quality products they need to complete their solutions. We offer an unmatched selection of computer parts, cables, server management solutions and A/V products and serve a worldwide market through our locations in the United States, Canada, the United Kingdom and Taiwan.

Visit **www.startech.com** for complete information about all our products and to access exclusive interactive tools such as the Parts Finder and the KVM Reference Guide. StarTech.com makes it easy to complete almost any IT solution. Find out for yourself why our products lead the industry in performance, support, and value.