

3 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT101HQ3



This 3ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Applications

- Extends VGA/SVGA monitor cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI
- Molded connector ends with strain relief

Technical Specifications

Warranty	Lifetime
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Male
Color	Black
Cable Length	3 ft [0.9 m]
Product Length	3 ft [0.9 m]
Product Weight	4.7 oz [134 g]
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	3 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Certifications, Reports and Compatibility

