

## 6 ft DB9 M/F Fibre Channel Cable

StarTech ID: FIBCLDB9MF6



Don't let cabling be the bottleneck that slows down your network. Our Fibre Channel cables offer superior performance, with up to 2 Gigabits/sec (duplex) of serial data transfer. With enhanced data transfer rates and increased reliability, these cables are the optimal solution when large-scale, high-speed data transfer is needed.

### Applications and Solutions

- High performance fibre channel cable designed for bi-directional, serial data communication between servers, mass storage subsystems and other peripherals (hubs, switches and point-to-point connections)
- Ideal for Storage Area Networks (SAN), Wide Area Networks (WAN), computer clusters and other data intensive computing environments

## Features

- Backed by StarTech.com lifetime warranty
- Data transfer rate of up to 2 Gbits/sec in full-duplex mode
- Data transfer rate of up to 2 Gbits/sec in full-duplex mode
- Flexible PVC jacket
- Ideal for serial data communication between servers, mass storage subsystems and other peripherals (hubs, switches and point-to-point connections) using Fibre Channel interface
- Supports SCSI RAID devices with Fibre Channel interface
- Works with existing SCSI drives and acts as a SCSI to Fibre Bridge

## Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - DB9 Male
- Connector B: 1 - DB9 Female
- Color: Black
- Product Length: 6 ft [1.83 m]
- Carton Quantity: 60
- Shipping (Package) Weight: 0.31 lb [0.14 kg]
- Length: 6 ft
- Connectors: Connector A: DB9 (Male)
- : Connector B: DB9 (Female)
- Jacket: PVC
- Conductor: 28 AWG
- Insulation: Polyolefin

