

## 25 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT101HQ\_25



This 25ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Applications

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

### Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

## Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Color	Black
Wire Gauge	28 AWG
Cable Length	25 ft [7.6 m]
Product Weight	2.1 lb [0.9 kg]
Shipping (Package) Weight	2.1 lb [0.9 kg]
Included in Package	1 - 25 FOOT COAXIAL CABLE
Included in Package	2 - Nuts

## Certifications, Reports and Compatibility

