

6 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

StarTech ID: MXT101MMHQ



The MXT101MMHQ 6-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Applications

- Ideal for high resolution monitors (1920x1200 and above)
- Connect any VGA display to a VGA source
- Connect a high resolution display to a Desktop PC or video switch, up to 6 feet away

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

Technical Specifications

| | |
|---------------------------|--|
| Warranty | Lifetime |
| Number of Conductors | 14 |
| Connector Plating | Nickel |
| Cable Jacket Type | PVC - Polyvinyl Chloride |
| Cable Shield Type | Aluminum-Mylar Foil with Braid |
| Fire Rating | CMG Rated (General Purpose) |
| Number of Ferrites | 1 |
| Regulatory Approvals | UL2919 |
| Connector A | 1 - VGA (15 pin; High Density D-Sub) Male |
| Connector B | 1 - VGA (15 pin; High Density D-Sub) Male |
| Impedance | 75 Ohm |
| Color | Black |
| Wire Gauge | 28 AWG |
| Max Connector Dimension | 1.3 in [34 mm] |
| Cable Length | 6 ft [1.8 m] |
| Cable OD | 0.4 in [9 mm] |
| Product Weight | 9.9 oz [280 g] |
| Operating Temperature | 0 to 60 5/23/2012eg;C |
| Storage Temperature | -20 to 80 5/23/2012eg;C |
| Humidity | 0 - 80 %RH |
| Shipping (Package) Weight | 0.6 lb [0.3 kg] |
| Included in Package | 1 - 6 ft Coax High Resolution VGA Monitor Cable - HD15 M/M |
| Included in Package | 2 - Nuts |

Certifications, Reports and Compatibility

