

**25 ft Coax High Resolution VGA Monitor Cable - HD15 M/M**

*StarTech ID: MXT101MMHQ25*



This 25ft High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA. Ideally suited for high resolution VGA applications, this high quality male to male coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

## Features

- Ferrite core eliminates EMI interference
- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 20
- Shipping (Package) Weight: 1.99 lb [0.9 kg]
- Cable Length: 25 ft [7.62 m]
- Connector A: 1 - 15 pin High Density D-Sub (VGA) Male
- Connector B: 1 - 15 pin High Density D-Sub (VGA) Male
- Wire Gauge: 28 AWG

