

10 ft Coax High Resolution 905/12/2012eg; Down Angled VGA Monitor Cable - HD15 M/M

StarTech ID: MXT101MMHD10



This 10ft High Resolution Video VGA Cable (90 degree) is designed to provide the highest video quality possible through a VGA connection and is specifically constructed to accommodate tight installation spaces.

The high quality, shielded coax VGA cable features a 90 degree down-angled plug, which requires only 32.4mm (1.27") of space to make the video connection.

More than suitable for high-res VGA applications (1280x1024 resolution and above), the 90 degree VGA cable eliminates picture "ghosting" and fuzzy images that are common with non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

This 10ft High Resolution Video VGA Cable (90 degree) is designed to provide the highest video quality possible through a VGA connection and is specifically constructed to accommodate tight installation spaces. Features a 90 degree down-angled plug.

Applications

- Connecting Multimedia Servers
- POS Displays
- Ideal for high resolution monitors (1280x1024 and above)
- Making VGA video connections in tight install spaces

Features

- Ferrite core
- Impedance matched at 75 Ohms
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire construction
- 905/12/2012eg; downward-angled connector with a 32.4mm depth

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Number of Ferrites	1
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	10 ft [3 m]
Product Weight	11.8 oz [334 g]
Shipping (Package) Weight	0.8 lb [0.4 kg]
Included in Package	1 - 10ft Coax High Resolution Down Angle VGA Monitor Cable

Certifications, Reports and Compatibility

