

6 ft Coax High Resolution 905/10/2012eg; Down Angled VGA Monitor Cable - HD15 M/M

StarTech ID: MXT101MMHD6



This 6ft High Resolution Video VGA Cable (90 degree) is designed to provide the highest video quality possible through a VGA connection and is specifically constructed to accommodate tight installation spaces.

The high quality, shielded coax VGA cable features a 90 degree down-angled plug, which requires only 32.4mm (1.27") of space to make the video connection.

More than suitable for high-res VGA applications (1280x1024 resolution and above), the 90 degree VGA cable eliminates picture "ghosting" and fuzzy images that are common with non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Applications

- Connecting Multimedia Servers
- POS Displays
- Ideal for high resolution monitors (1280x1024 and above)
- Making VGA video connections in tight install spaces

Features

- 905/10/2012eg; downward-angled connector with a 32.4mm depth
- Ferrite core
- Ideal for high resolution monitors (1280x1024 and above)
- Impedance matched at 75 Ohms
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire construction

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Number of Ferrites	1
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	6 ft [1.8 m]
Product Weight	5.5 oz [156 g]
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - 6ft Coax High Resolution Down Angle VGA Monitor Cable

Certifications, Reports and Compatibility

