

50 ft Coax High Resolution VGA Monitor Cable - HD15 M/M

StarTech ID: MXT101MMHQ50



The MXT101MMHQ50 50-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Applications

- Ideal for high resolution monitors (1920x1200 and above)
- Connect any VGA display to a VGA source
- Connect a high resolution display to a Desktop PC or video switch, up to 50 feet away

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

Technical Specifications

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1
Regulatory Approvals	UL2919
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Impedance	75 Ohm
Color	Black
Wire Gauge	28 AWG
Max Connector Dimension	1.3 in [34 mm]
Cable Length	50 ft [15.2 m]
Cable OD	0.4 in [9 mm]
Product Weight	3.8 lb [1.7 kg]
Operating Temperature	0 to 60 °C
Storage Temperature	-20 to 80 °C
Humidity	0 - 80 %RH
Shipping (Package) Weight	3.8 lb [1.7 kg]
Included in Package	1 - 50 ft Coax High Resolution VGA Monitor Cable - HD15 M/M
Included in Package	2 - Nuts

Certifications, Reports and Compatibility

