

15 ft Coax VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT105HQ



This 15ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by up to 15ft, while maintaining superb image quality.

Applications

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

Features

- Ideal for high resolution monitors (1024x768 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Color	Gray
Cable Length	15 ft [4.6 m]
Product Weight	1.3 lb [0.6 kg]
Shipping (Package) Weight	1.3 lb [0.6 kg]
Included in Package	1 - 15 FT COAXIAL SVGA CABLE
Included in Package	2 - Nuts

Certifications, Reports and Compatibility

