

1 Port PCI Dual Voltage Parallel Adapter Card

StarTech ID: PCI1PECPDV



The PCI1PECPDV PCI Dual Voltage EPP/ECP Parallel Adapter Card adds an IEEE 1284 port to your PC using either a PCI 5V or PCI-X 3.3v slot, with support for data transfer speeds of up to 1.5 Mbps – up to 3 times faster than built-in parallel ports.

The adapter card supports Windows® Vista™, XP, ME, 2000, 98SE, NT4, DOS® and Linux®. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

This PCI Parallel adapter card is a complete dual profile solution, providing both a standard bracket and a low profile/half-height bracket for adapting to slimline or small form-factor system applications.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications and Solutions

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Supports 3.3 and 5V PCI slots
- Maximum data transfer rate of 1.5 Mbps
- Standard and low-profile bracket included
- IRQ sharing eliminates conflicts between multiple cards
- PCI 2.2 and PCI Power Management 1.0 compliant
- SPP/EPP/ECP Parallel port that fully supports existing Centronics interface

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI / PCI-X (5 / 3.3V)
- Chipset ID: Oxford: OX16PCI1952
- Connector Types: 1 - DB25 Female
- Carton Quantity: 48
- Shipping (Package) Weight: 0.31 lb [0.14 kg]
- Bus Type: PCI 5V / PCI-X 3.3V
- Maximum Data Transfer Rate: 1.5 Mbps
- OS Compatibility: Windows 95/ 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, and Linux 2.4.x and up

