


## 1 Port PCI RS232 Powered Serial Adapter Card

StarTech ID: PCI1S650PW



This PCI-based RS232 Powered Serial Adapter Card offers an easy way to add self-powered serial devices to your computer, POS solution, or manufacturing application.

The adapter provides a high-performance serial port that can be configured to deliver 5 or 12 volts of power to compatible devices, and for additional flexibility, this card can be used in PCI (5 volt) or PCI-X (3.3 volt) expansion slots and supports Windows (including 64-bit editions) and Linux environments.

### Applications and Solutions

- Perfect for adding barcode scanners, card readers, and other similar devices to POS, manufacturing, and industrial solutions.
- Reduce clutter and the need for extra power connections by using self-powered serial devices.

## Features

- Configurable in 5V, 12V, and RI (non-powered) modes.
- Supports major operating systems, including 64-bit editions of Microsoft Windows.
- Works in both PCI and PCI-X slots, either standard or low profile.

## Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI / PCI-X (5 / 3.3V)
- Connector Types: 1 - DB9 Male
- Product Height: 1.97 in [50 mm]
- Product Length: 4.72 in [120 mm]
- Maximum Data Transfer Rate: 920000 Kbits/Sec
- Number of Ports: 1
- Operating Temperature: 0-57
- Carton Quantity: 50
- Shipping (Package) Weight: 0.38 lb [0.17 kg]
- Product Weight: 1.76 oz [50 g]
- Microsoft WHQL Certified: Yes
- Product Width: 0.67 in [17 mm]
- FIFO: 32 byte (hardware) / 128 Kbytes (via Windows software driver)
- UART: 16C650 UART compatible
- Internal connector: Internal SP4 power connector for additional power demands
- Chipset ID: Sunix - SUN1889
- OS Compatibility: DOS, Windows 95/ 98SE/ ME/ NT/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, and Linux  
Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS/ CE 5.0/ CE 6.0

