


2 Port PCI Parallel Adapter Card - EPP/ECP

StarTech ID: PCI2PECP



The PCI2PECP 2 Port EPP/ECP PCI Parallel Adapter Card can be installed in an available PCI slot to add two IEEE 1284 ports to your PC, supporting data transfer speeds of up to 1.5 Mbps (up to 3 times faster than built-in parallel ports).

Installing the EPP/ECP parallel adapter card is easy, with support for Windows® Vista, XP, ME, 2000, 98, 95, NT4, DOS® and Linux®. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

A complete dual profile solution, this parallel adapter card provides both a standard bracket and a low-profile/half-height bracket for adapting to slimline or small form factor system applications.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications and Solutions

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Compatible with Linux and all versions of Windows® including Windows® XP
- Data transfer rates of up to 1.5 Mbps
- Easy plug and play installation
- Includes half-height/low profile mounting bracket
- Installation scripts available for Linux RedHat 7.2, SuSE 7.3 and Mandrake 8.2
- IRQ sharing eliminates conflicts between multiple cards
- Supports EPP, ECP, SPP and BPP

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI (5 Volt)
- Connector Types: 2 - DB25 Female
- Maximum Data Transfer Rate: 1.5 Mbps
- Number of Ports: 2
- Carton Quantity: 40
- Industry Standards: SPP
- Industry Standards: PS2
- Industry Standards: BPP
- Industry Standards: EPP
- Industry Standards: ECP
- Industry Standards: IEEE-1284
- Shipping (Package) Weight: 0.46 lb [0.21 kg]
- Card Type: Low / Standard Profile
- Chipset ID: MosChip MCS9815/NM9715
- OS Compatibility: MS DOS, Windows 95/ 98SE/ ME/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux

