


2 Port PCI Express Parallel Adapter Card - EPP/ECP

StarTech ID: PEX2PECP



The PEX2PECP PCI Express based EPP/ECP/SPP parallel card adds two IEEE 1284 parallel ports to your PC, with support for parallel data communication at speeds of up to 1.5 Mbps – up to 3 times faster than on-board parallel ports!

Installation is a breeze with support for Windows® 7, Vista, XP, 2003 and 2000. IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connection to any parallel peripheral.

The 2 port PCI Express Parallel adapter card is a complete dual profile solution, providing both standard bracket and low profile brackets for adapting to slimline or small form factor system applications.

Backed by a StarTech.com Lifetime Warranty and free lifetime technical support.

Applications and Solutions

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Supports Standard Parallel Port(SPP), Enhanced Parallel Port(EPP) & Enhanced CapabilityPort(ECP)
- Data transfer rate up to 1.5 Mbps
- Compliant with PCI Express Base Specification 1.0a

Technical Specifications

- Warranty: Lifetime warranty
- Connector Types: 2 - DB25 Female
- Product Height: 4.72 in [120 mm]
- Product Length: 3.62 in [92 mm]
- Carton Quantity: 60
- Shipping (Package) Weight: 0.44 lb [0.2 kg]
- Product Weight: 3.35 oz [95 g]
- Product Width: 0.83 in [21 mm]
- General Specifications: Single 3.3V-5.0V operation (RoHS)
- Card Type: Low / Standard Profile
- Maximum Data Transfer Rate: 1.5 Mbps
- Chipset ID: MosChip MCS9815CV
- OS Compatibility: DOS, Windows 95/ 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux Kernel 2.6.11 and above,

