


## 2S1P Native PCI Express Parallel Serial Combo Card with 16550 UART

StarTech ID: PEX2S5521P



The PEX2S5521P 2S1P PCI Express Card turns a PCI Express slot into two RS232 (DB9) serial ports and one Parallel port. The adapter card features a native PCI Express single chip design that allows you to take advantage of full PCI Express capability, providing improved speed and reliability while reducing the load applied to the CPU by as much as 48% over conventional serial cards which use a bridge chip design.

Compatible with a broad range of operating systems including Windows 2000/XP/2003/Vista/Windows 7/Server 2008 R2 (32 and 64 bit), Linux Kernel 2.6.11 and up, and MAC OS 10.4, this 2 Port Serial 1 Port Parallel PCI-Express Card also features an optional low profile bracket that allows the card to be installed in virtually any computer case, regardless of the case form factor.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

### Applications and Solutions

- Self service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers
- POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers / card swipes, scales, and elevated displays on poles

- Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads
- Standard ATM automated teller machines to control keypads, receipt printer, card readers / card swipes, touchscreen LCD's, camera control, etc.
- Used to control multiple surveillance / security cameras in a parking structure, office building, etc.

## Features

- Two high speed RS-232 serial ports with data transfer rate up to 460.8 Kbps
- One parallel port with data transfer rate up to 1.5 Mbps
- Compliant with PCI Express base specifications revision 1.0a
- 128-byte deep FIFO per transmitter and receiver
- Configurable in 5V, 12V, and RI (non-powered) modes.
- Selectable power output on pin 9 for the serial port
- Native single-chip, single lane PCI Express
- Automated out-of-band flow control using CTS/RTS and DSR/DTR
- Automated in-band flow control using programmable Xon/Xoff in both directions

## Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI Express
- Connector Types: 1 - DB25 Male
- Connector Types: 2 - DB9 Male
- Product Height: 0.79 in [20 mm]
- Product Length: 4.13 in [105 mm]
- Number of Ports: 2
- Carton Quantity: 50
- Shipping (Package) Weight: 0.55 lb [0.25 kg]
- Product Weight: 4.94 oz [140 g]
- Product Width: 4.72 in [120 mm]
- Bus Type: PCI Express
- General Specifications: Readable flow control status and FIFO levels
- Supports: x1, x2, x4, x8, x16(lane)
- Maximum Data Transfer Rate:
  - RS-232: 460.8 Kbps
  - Parallel: 1.5 Mbps
- Note: Selectable power output on pin 9 of the serial port
- Chipset ID: MosChip MCS9901
- OS Compatibility: DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.4.x and up  
Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS/ CE 5.0/ CE 6.0

