

2 Port PCI Express Parallel Adapter Card - EPP/ECP

StarTech ID: PEX2PECP



The PEX2PECP PCI Express based EPP/ECP/SPP parallel card adds two IEEE 1284 parallel ports to your PC, with support for parallel data communication at speeds of up to 1.5 Mbps – up to 3 times faster than on-board parallel ports!

Installation is a breeze with support for Windows® 7, Vista, XP, 2003 and 2000. IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connection to any parallel peripheral.

The 2 port PCI Express Parallel adapter card is a complete dual profile solution, providing both standard bracket and low profile brackets for adapting to slimline or small form factor system applications.

Backed by a StarTech.com Lifetime Warranty and free lifetime technical support.

Applications

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Supports Standard Parallel Port(SPP), Enhanced Parallel Port(EPP) & Enhanced Capability Port(ECP)
- Data transfer rate up to 1.5 Mbps
- Compliant with PCI Express Base Specification 1.0a

Technical Specifications

Warranty	Lifetime
Ports	2
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Chipset ID	ASIX/MosChip - MCS9815CV
Connector Type(s)	1 - PCI Express x1 Male
External Ports	2 - DB-25 (25 pin; D-Sub) Female
Maximum Data Transfer Rate	1.5 Mbps
OS Compatibility	DOS, Windows 95/ 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux Kernel 2.6.11 and above,
Product Length	3.6 in [92 mm]
Product Width	0.8 in [21 mm]
Product Height	4.7 in [120 mm]
Product Weight	3.4 oz [95 g]
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - 2 Port PCIe Parallel Card
Included in Package	2 - Low Profile Brackets
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

