

12U 19in Hinged Wall Mount Server Rack Cabinet w/ Steel Mesh Door

StarTech ID: RK1219WALHM



This 12U Server Rack/Cabinet offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle.

The sturdy 12U rack cabinet features a high quality steel design and a vented, steel mesh door to help keep rack mounted equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack cabinet accommodates 19in wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

Our 12U Rack Cabinet is designed for guaranteed reliability to ensure a stable rack mount platform for valuable equipment and backed by Lifetime Warranty.

Applications

- Mounting standard 19 in. networking equipment in exposed or unsecure locations

Features

- Unique hinged design swings open for easy access to your equipment
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Steel mesh door for added security

Technical Specifications

Warranty	Lifetime
U Height	12U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel Mesh
Side Panel Type	Solid Steel
Key Lock	Yes
Industry Standards	EIA RS310-C
Fan(s)	Optional
Weight Capacity	132.6 lb [60 kg]
Color	Black
Internal Width	18.3 in [465 mm]
Internal Height	21 in [533.4 mm]
External Width	23.6 in [600 mm]
External Height	25 in [635 mm]
External Depth	21.7 in [550 mm]
Product Weight	65.2 lb [29.5 kg]
Maximum Mounting Depth	16.2 in [412.8 mm]
Flat Pack	No
Shipping (Package) Weight	68.5 lb [31 kg]
Included in Package	1 - Black Hinged Cabinet
Included in Package	1 - Set of Keys
Included in Package	1 - Package of Cab Screws and Cage Nuts