

## VGA over Cat5 Video Extender Receiver

StarTech ID: ST121REU



The ST121REU VGA over Cat5 Video Extender Receiver is specifically designed for use as the receiver unit to the StarTech.com [ST1214TEU](#) 4 Port VGA over Cat5 UTP Extender transmitter, allowing you to split and extend a single VGA source to up to four remote displays.

From the transmitter device, the VGA video signal is sent over standard 4 pair Category 5 or better UTP cable to remote monitors, each connected to an ST121REU Cat 5 VGA receiver - supporting distances of up to 150 meters (500 feet).

A cost-effective video extension solution, this receiver is ideal for a wide range of environments including airports, bus depots, retail, or any large buildings where VGA video needs to be extended to long connection distances.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications and Solutions

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

## Features

- Extends video cables by up to 500 ft. (150m)
- Provides crystal clear picture quality
- Pure hardware design, no software or drivers required
- Supports VGA, SVGA, and Multisync monitors
- Uses standard Cat 5 or better cabling
- Supports 1024x768 resolution at 150 ft. (50m)

## Technical Specifications

- Warranty: 2 Years
- Product Height: 0.81 in [20.55 mm]
- Product Length: 3.31 in [84.16 mm]
- Maximum Cable Length: 152400
- Maximum Analog Resolutions: 1024 x 768 @ 500 feet (150m)
- Output Current: 600mA
- Power Adapter - Amperage: 600mA
- Power Adapter - DC Voltage: 9V DC
- Carton Quantity: 12
- Shipping (Package) Weight: 1.33 lb [0.6 kg]
- Product Weight: 6.04 oz [171 g]
- Product Width: 2.56 in [65.09 mm]

