

12U 19in Hinged Wall Mount Server Rack Cabinet w/ Vented Glass Door

StarTech ID: RK1219WALH



This 12U Rack offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle. The sturdy 12U rack features a high quality steel design and a vented, tempered glass door to help keep your rack mount equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack accommodates 19" wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations

Features

- Unique hinged design swings open for easy access to a your equipment
- Removable side panels with lock.
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Sturdy steel design
- Tempered, vented, lockable glass front door

Technical Specifications

Warranty	Lifetime
U Height	12U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel w/ Window
Side Panel Type	Solid Steel
Key Lock	Yes
Industry Standards	EIA RS310-C
Fan(s)	Optional
Weight Capacity	132.6 lb [60 kg]
Color	Beige
Internal Width	18.3 in [465 mm]
External Width	23.6 in [600 mm]
External Height	25 in [635 mm]
External Depth	21.7 in [550 mm]
Maximum Mounting Depth	16.2 in [412.8 mm]
Flat Pack	No
Shipping (Package) Weight	68.2 lb [30.9 kg]
Included in Package	1 - 12U Server Cabinet
Included in Package	2 - Sets of Keys

Certifications, Reports and Compatibility

