

## 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket

StarTech ID: RK319WALLV



The RK319WALLV 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 3U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design, perfect for SoHo (small office, home office) environments. The wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com lifetime warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

### Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

## Features

- Constructed to meet the EIA-310 19" rack standards
- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack
- Equipment can be vertically wall mounted, or horizontally under a desk
- Compatible with most 19" rack mountable equipment
- Made from solid steel for durability
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs

## Technical Specifications

Warranty	Lifetime
U Height	3U
Frame Type	Open Frame
Wallmountable	Yes
Front Door Type	Open
Industry Standards	EIA RS310-C
Fan(s)	No
Weight Capacity	125.3 lb [56.7 kg]
Color	Black
Internal Width	18.3 in [465 mm]
External Width	19.8 in [504 mm]
External Height	5.9 in [149 mm]
External Depth	5.9 in [151 mm]
Product Weight	33.2 oz [940 g]

**Note** Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials

Flat Pack	No
Shipping (Package) Weight	3.1 lb [1.4 kg]
Included in Package	1 - Vertical Wall Mount Bracket
Included in Package	12 - Cage nuts and screws (12 Each)
Included in Package	6 - Self Tapping Wood Screws - 3/16" x 1 1/2"

Certifications, Reports and Compatibility

