

Gigabit 850nm Multi Mode SFP Fiber Optical Transceiver - LC 550m

StarTech ID: SFPSXMM



The SFPSXMM Gigabit 850nm Multi Mode SFP Fiber Optical Transceiver - LC 550m offers a cost-effective way to increase performance and connectivity of your fiber-connected network devices.

Using a short wavelength (850nm) VCSEL laser diode, enabling a maximum cable distance of 550m (0.3 miles) over multi mode fiber, this Small Form Factor Pluggable (SFP) Gigabit Multi Mode module can be installed into any fiber networking devices with an SFP Multi-Sourcing Agreement (MSA) compliant port, providing a simple solution to upgrade existing network devices to connect to remote locations using LC terminated multimode fiber.

Delivering convenience and scalability, the optical transceiver allows you to install the multimode LC module without interrupting network traffic or requiring a device reboot.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Perfect for network extension and fiber backbones
- Replacing defective or damaged SFPs in MSA compliant equipment
- Use in Multimode fiber installations
- Expand your network to remote segments over fiber

Features

- 1.25Gbps IEEE 802.3z 1000BASE-SX Compliant
- Complies with SFP Multi-Source Agreements standards (MSA)
- Equipped with a 850nm VCSEL Laser with Class 1 laser safety standards IEC825 compliance
- Duplex LC receptacle connector
- Complies with 1.0625Gbps Fiber Channel **FC-PI 100-M5-SN-I** and **FC-PI 100-M6-SN-I**
- Serial ID functionality support
- Fully Hot Pluggable

Technical Specifications

Warranty	2 Years
Industry Standards	IEEE 802.3z 1000BASE-SX
Remote Unit Connectors	1 - Fiber Optic LC Female
Maximum Data Transfer Rate	1000Mbps
Max Transfer Distance	550 m (1804 ft)
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
Product Length	2.2 in [55 mm]
Product Width	0.5 in [13 mm]
Product Height	0.4 in [9 mm]
Product Weight	0 lb [0 kg]
Operating Temperature	05/9/2012eg;C to 705/9/2012eg;C (325/9/2012eg;F to 1585/9/2012eg;F)
Storage Temperature	-405/9/2012eg;C to 855/9/2012eg;C (-405/9/2012eg;F to 855/9/2012eg;F)
Humidity	5 to 95% RH
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - SFP Multimode LC Transceiver

Certifications, Reports and Compatibility

