

8 Port VGA Video Splitter & Distribution Amplifier - 250 MHz

StarTech ID: ST128



The StarTech.com VideoView is a 8 port VGA Video Splitter that allows a PC to display to as many as 8 monitors simultaneously. It is perfect for classrooms, tradeshow, or in-store displays where high quality video on several monitors is needed. The VideoView supports monitors with up to 200MHz of bandwidth allowing it to display images of up to 1600 x 1200 pixels. A built-in booster circuit allows the video signal to be extended up to 200 ft.

Applications

- Public information display services
- Public broadcast systems
- Demos and presentations
- In-store product merchandising
- Information kiosks

Features

- Allows one computer to provide simultaneous displays on several different monitors
- Works with VGA, SVGA and Multisync monitors
- Daisy chainable for almost unlimited expansion
- Built-in video amplifier boosts the signal to allow a cable length of up to 210 ft or 65m
- Uses standard monitor extension cables
- High/Low Level Brightness control
- Includes AC 120V power adapter

Technical Specifications

Warranty	2 Years
Ports	8
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Male
Connector Type(s)	8 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	1600x1200
General Specifications	(8) High Density DB15 Female
General Specifications	1200g
General Specifications	1600x1200 @ 60Hz
General Specifications	200 MHz
General Specifications	224x152x52 mm
General Specifications	5~40 deg C, 0~80% RH non-condensing
General Specifications	65m (210 ft.) maximum
General Specifications	FCC Part 15 Class A, CE Mark
General Specifications	High Density DB15 Male
General Specifications	XGA, VGA, SVGA, Multisync Monitor
Color	Black
Product Length	8.8 in [224 mm]
Product Width	6 in [152 mm]
Product Height	2 in [52 mm]
Product Weight	42.4 oz [1200 g]
Power Adapter Included	Yes
Input Voltage	9
Shipping (Package) Weight	4.1 lb [1.8 kg]
Included in Package	1 - SWITCH
Included in Package	1 - POWER ADAPTOR
Included in Package	1 - INSTRUCTION MANUAL

Certifications, Reports and Compatibility



