

2 Port VGA Video Splitter - USB Powered

StarTech ID: ST122LE



This 2-Port VGA Video Splitter allows a computer to display VGA video on two monitors simultaneously.

Perfect for classrooms, tradeshows, or any environment requiring high quality video on several monitors, the ST122LE VGA splitter supports displays with up to 300 MHz of bandwidth and up to 2048x1536 resolution. Plus, to simplify placement of your VGA displays, the splitter features a built-in booster circuit that allows you to locate VGA monitors up to 200 ft away from your system, and can be powered through a USB connection to the host computer, eliminating the need to find an available power outlet.

Application Diagram



The ST122LE VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Supports resolutions up to 2048 x 1536 @60Hz
- USB-Powered
- Our most compact VGA splitter
- 300 MHz video bandwidth
- Integrated signal amplifier boosts your connection range to 210 feet (65 meters)
- Supports DDC, DDC2, DDC2B (For video out port 1)

Technical Specifications

Warranty	2 Years
Ports	2
Industry Standards	DDC, DDC2, DDC2B, on Video Out Port 1
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	2 - VGA (15 pin; High Density D-Sub) Female
Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	2048x1536
Bandwidth	300MHz
MTBF	40,000 Hours
Color	Black
Enclosure Type	Plastic
Power Adapter Included	Self Powered
Output Voltage	5 DC
Output Current	0.5A
Operating Temperature	05/11/2012eg;C to 705/11/2012eg;C (325/11/2012eg;F to 1585/11/2012eg;F)
Storage Temperature	-205/11/2012eg;C to 855/11/2012eg;C (-45/11/2012eg;F to 1855/11/2012eg;F)
Humidity	0% - 95%
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - Video Splitter
Included in Package	1 - USB to DC power adapter
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

