

## 4 Port DVI-I Video Splitter - Digital and Analog

StarTech ID: ST124DVI



This DVI splitter lets you share DVI video signals between four displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source, while maintaining high definition display resolutions up to 1080p.

A simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments), the DVI splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

Designed to provide dependable performance, the DVI splitter/signal distribution amplifier is backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

### Applications

- Connect DVI enabled projectors, monitors, plasma screens, commercial billboards, and wall display systems
- Ideal for graphic design, classroom use and training seminars
- Great for use in tradeshow, POS, healthcare, airport, train station and bus terminal settings

### Features

- Supports resolutions of up to 1600 x 1200 pixels @ 60 Hz
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Fully compliant with the DVI 1.0 standard established by the DDWG
- Simple setup for quick connection in minutes

## Technical Specifications

Warranty	2 Years
Ports	4
Connector Type(s)	3 - DVI-I (29 pin) Female
Maximum Analog Resolutions	1600x1200
	Note that this product is not intended for use with widescreen displays.
Cable Distance - Source to Display	Max of 33ft (10m)
Height	1.65 Inches (42 mm)
Industry Standards	DVI 1.0
Input Connector	1 x 24-pin DVI-I
LED Indicators	1 x Power
Length	10.5 Inches (268 mm)
Max Resolution	1600 x 1200 @ 60Hz
Output Connector	2 x 24-pin DVI-I
Power Adapter	7.5V DC (1.5A)
Video Bandwidth	25 ~ 165 MHz (VGA ~ UXGA)
Weight	2.6 lbs (1.24 kg)
Width	4.25 Inches (105 mm)
Color	Gray
Product Length	10.6 in [268 mm]
Product Width	4.1 in [105 mm]
Product Height	1.7 in [42 mm]
Product Weight	43.8 oz [1240 g]
Input Voltage	7.5
Input Current	1.5
Shipping (Package) Weight	4.2 lb [1.9 kg]

## Certifications, Reports and Compatibility



