

2 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub

StarTech ID: SV231DD2DUA



The SV231DD2DUA 2-port Dual DVI USB KVM Switch allows two PCs, each with dual DVI video outputs, to share two monitors, one microphone and set of speakers, one keyboard and one mouse as well as two other USB peripherals.

An ideal solution for graphic designers, CAD/CAM designers or educational and financial institutions, the dual view KVM Switch allows you to instantly switch back and forth between dual DVI display PCs at the touch of a button, while maintaining professional level video quality on both monitors. The dual DVI switch also features an integrated USB hub port that allows USB 2.0 peripherals such as thumb drives, external hard drives or web cams to be shared between attached systems - eliminating duplicate peripheral costs.

Please Note: While both DVH (analog mode) and DVI-D (digital only) are supported by the KVM, both source PCs should output the same signal type for proper switching. It is recommended wherever possible to use DVI-D cables across all PC to KVM and KVM to Console connections. Please contact technical support if you require assistance identifying your source.

Backed by a StarTech.com 3 year warranty and free lifetime technical support.

Applications

- Dual system control for single user workstations with dual head video cards, increasing user productivity in the office
- Control two dual display multimedia computers with a single set of console peripherals (Keyboard, Mouse, and two Monitors)
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications, and multiple screens
- Integrated USB 2.0 hub and Mic/Audio switching allows the user to have full multimedia control of two computers and share USB peripherals

Features

- Front panel push-buttons and Hot-key functions for easy switching
- Supports resolutions up to 2048x1536 (Analog) and 1920x1200 (digital)
- USB 2.0 hub for peripheral sharing (Thumb drives, external hard drives, web cams, etc.)
- Audible tone confirms port switching
- Combined or independent switching of audio and/or USB hub ports
- EDID retention - eliminates hassle when switching between computers as the KVM "remembers" monitor settings
- Supports all USB-capable operating systems (Windows 98e/SE/ME/2000/XP/Vista/7, Linux, Mac OS, etc.)
- Rugged, all-metal chassis for use in harsh environments
- TMDS compliant to support DDC2B emulation and HDCP for digital contents protection
- Status LED display for easy port status monitoring

Technical Specifications

Warranty	3 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Multi-Monitor	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - DVH (29 pin) Female
Console Interface(s)	4 - USB A (4 pin) Female
Host Connectors	2 - USB B (4 pin) Female
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position) Female
Host Connectors	4 - DVH (29 pin) Female
DVI Support	Yes - Single Link
IP Control	No
Maximum Analog Resolutions	2048 x 1536
Maximum Digital Resolutions	1920 x 1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
Color	Black
Enclosure Type	Steel
Product Length	6.4 in [163 mm]
Product Width	6.3 in [160 mm]
Product Height	2.2 in [57 mm]
Product Depth	3.9 in [100 mm]
Product Weight	26.5 oz [750 g]
LED Indicators	1 - Green - Power
LED Indicators	4 - Green - Host Online, Red - Host Selected
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.8A
Output Voltage	12 DC

Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Operating Temperature	05/11/2012eg;C to 405/11/2012eg;C (325/11/2012eg;F to 1045/11/2012eg;F)
Storage Temperature	-205/11/2012eg;C to 605/11/2012eg;C (-45/11/2012eg;F to 1405/11/2012eg;F)
Humidity	90% RH
Shipping (Package) Weight	2.6 lb [1.2 kg]
Included in Package	1 - Two Port Dual DVI KVM
Included in Package	1 - Rubber Feet
Included in Package	1 - Universal Power Adapter (US/UK/EU)
Included in Package	1 - Manual

Certifications, Reports and Compatibility

