

## VGA to Component (YPbPr) Video Converter

StarTech ID: VGA2CPNT



This VGA to Component (YPbPr) Video Converter allows you to convert a VGA signal (VGA, 640x480) and XGA signal (XGA, 1024x768) to component (YPbPr) video.

Installation couldn't be simpler - this product allows you to use a completely hardware solution to convert VGA video to Component, which requires no driver or software installation.

Please note that the VGA to Component (YPbPr) Video Converter does not provide video scaling. Scaling will have to be performed by the display being used; for example, a 1024x768 signal will need to be scaled to 720p by the display.

## Features

- Convert a VGA signal to a component signal.
- Output a component signal to standard and high definition televisions using 480i/480p/720p

## Technical Specifications

- Warranty: 1 Year warranty
- Input Connector: 1 x HD15 VGA/RGBHV
- Output Connector: 1 x Component (YPbPr) and one H+V for RGBHV.
- Input Current: Input Signals: VGA (640x480), XGA (1024x768), and YPbPr
- Output Signals: 480p and 720p
- Power Adapter: 5V DC 2.6A power adapter. Comes with universal power supply clips for Europe.
- Enclosure Type: Aluminum
- Product Height: 1.18 in [30 mm]
- LED Indicators: 1 - Power LED
- Product Length: 4.13 in [105 mm]
- Center Tip Polarity: Positive
- Carton Quantity: 30
- Shipping (Package) Weight: 1.08 lb [0.49 kg]
- Product Weight: 14.12 oz [400 g]
- Product Width: 2.99 in [7.6 cm]

