

## SATA USB Adapter Cable with Power Adapter

StarTech ID: USB2SATA25



The USB2SATA25 USB-SATA Adapter Cable connects any standard 2.5in or 3.5in SATA hard drive to a computer through USB 2.0.

The USB to SATA adapter lets you connect a bare drive with no enclosure, saving time and hassle.

The adapter cable works with Windows and Mac computers and does not require driver installation - a true plug-and-play solution for adding cost-effective external storage or overcoming incompatibility between modern hard drives and motherboards that may not be SATA-equipped or have a Serial ATA port available.

### Applications and Solutions

- Connect a 2.5 inch or 3.5 inch SATA drive to a USB 2.0 port
- Plug in a Serial ATA hard drive quickly and easily without taking your case apart
- Testing and quickly swapping SATA hard drives
- Use your 2.5" and 3.5" SATA hard drives externally, with a laptop or desktop computer

## Features

- External power adapter included for connecting 3.5in SATA drives
- Included software for Windows enables cloning and one button backup feature for backing up and syncing files
- Includes all necessary interface and power connectors for your drives making it an all-in-one solution

## Technical Specifications

- Warranty: 1 Year warranty
- NOTE: USB2SATA25 is backwards compatible with USB 1.1 standard, but not recommended due to slow transfer rate.
- Color: Black
- Connector Types: 1 - USB A Male
- Connector Types: 1 - SATA Data 7 pin Male
- Connector Types: 1 - SATA Power Male
- Product Height: 0.71 in [18 mm]
- Input Current: 100-240VAC 50/60 Hz
- Product Length: 10.47 in [266 mm]
- Output Current: 2 Amps
- Plug Type: M
- Power Adapter Included: Yes
- Center Tip Polarity: Positive
- Carton Quantity: 10
- Shipping (Package) Weight: 0.99 lb [0.45 kg]
- Product Weight: 1.59 oz [45 g]
- Product Width: 2.17 in [55 mm]
- Maximum Data Transfer Rate: 480 Mbits/Sec
- Power Mode: USB bus powered for 2.5 inch hard drive. Requires included power adapter for 3.5 inch hard drives and 5.25 inch optical drives.
- Output Voltage: 12 DC
- Humidity: 0~80% RH
- Operating Temperature: 10°C to 40°C (50°F to 104°F)
- Storage Temperature: -10°C to 80°C (14°F to 176°F)
- OS Compatibility: Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 9.22 and up

