

1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

StarTech ID: VGABNCMF1



The VGABNCMF1 1-foot Coax HD15 VGA to 5 BNC RGBHV Adapter Cable features an HD15 VGA (male) connector and 5 BNC (RGBHV) (female) connectors, allowing you to connect your existing BNC video source to a VGA distribution amplifier or PC.

The cable can also be used with a VGA out signal, breaking out to 5 BNC female connectors that can be used with a 5 BNC (M-M) cable for use with a BNC monitor/display.

Applications

- Connect your BNC connected cabled panels and projectors to a VGA distribution amplifier or PC

Features

- Short flexible cable design
- HD15 VGA Male to 5 BNC Female Connectors

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	5 - BNC (RF Coax) Female
Color	Black
Wire Gauge	28 AWG
Cable Length	1 ft [0.3 m]
Cable OD	0.3 in [8.5 mm]
Product Weight	3.4 oz [96 g]
Note	RGB signal: Red, Green, Blue wires, Vertical Sync: Black wire, Horizontal Sync: White wire
Shipping (Package) Weight	3.7 oz [105 g]
Included in Package	1 - 1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Certifications, Reports and Compatibility

