

RKPW247015

24-Outlet 120V 15A Rackmount Power Strip

StarTech.com

Hard-to-find made easy


Quick Installation Guide

Packaging Contents

- 1 x Power Strip
- 4 x Mounting Bracket
- 4 x Mounting Screw
- 4 x Backing Plate

System Requirements

- 42U of available internal Rack/Cabinet space
- 120VAC electrical outlet with NEMA 5-15 connector



Installation

1. Locate an appropriate spot inside the rack to mount the power strip, such as vertical side-mounting rails.

NOTE: The power strip can be mounted vertically or horizontally to other surfaces, however mounting “up-side down” with the power sockets facing downwards is not recommended. The weight of the power strip and connected cables/peripherals in addition to any downward force (i.e. the force of pulling cables from the power sockets) could dislodge the power strip from the brackets.

2. Attach the mounting brackets to the rack first, using the provided screws and backing plate. Place the backing plate behind the rack’s mounting post and place the mounting bracket in front. The screw threads in from the mounting bracket side. Ideally the mounting brackets should be evenly spaced across the entire length of the power strip to provide the most stability.

3. The power strip can be snapped into the mounting brackets. There are small grooves that run along the sides of the power strip that the brackets latch onto.

4. Plug the power strip into an electrical outlet and toggle the power switch to the ‘on’ position to energize the strip.

Manual Revision:01/18/2011

For the most up-to-date information, please visit www.startech.com

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com’s lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.