

Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/ST - 10 m

Product ID: 50FIBLCST10



The 50FIBLCST10 10m LSZH LC to ST Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication

Features

- 1x LC MM male connector
- 1x ST MM male connector
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

Hardware	Warranty	Lifetime
	Fiber Size	50/125
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Performance	Cable Rating	1Gbps / 10Gbps
	Fiber Classification	OM2
	Fiber Type	Multi Mode
	Maximum Data Transfer Rate	10Gbps
Connector(s)	Connector A	1 - Fiber Optic LC Duplex Male
	Connector B	1 - Fiber Optic ST Duplex Male
Physical Characteristics	Cable Length	32.8 ft [10 m]
	Color	Orange
	Product Length	32.8 ft [10 m]
	Product Weight	0.3 lb [0.1 kg]
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	0.3 lb [0.1 kg]
What's in the Box	Included in Package	1 - 10m Multimode 50/125 Duplex Fiber Patch Cable LC - ST

Product appearance and specifications are subject to change without notice.