

10U 19in Wall Mounted Server Rack Cabinet

Product ID: CAB1019WALL



The CAB1019WALL 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server rack offers 10U of storage space and is designed to accommodate standard 19in (wide) rack equipment. To ensure a cool operating environment for your equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network and server equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open from the left or right as needed.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Features

- Fully adjustable mounting rails inside cabinet
- Front door is removable and can be switched to open left or right
- TAA compliant for GSA Schedule purchases
- Includes one, roof-mounted 5" (12cm) fan for up to 85 CFM of airflow
- Ships fully assembled and ready to use
- Includes a lockable & removable smoked acrylic front door with 2 keys
- Stylish enclosure is designed for durability and easy accessibility

Hardware	Warranty	Lifetime
	Adjustable Mounting Rails	No
	Cable Management	No
	Casters	No
	Fan(s)	Yes
	Fans	1 - 5in
	Frame Type	Enclosed Cabinet
	Front Door Construction	Glass
	Front Door Key Lock	Yes
	Front Door Reversible and/or Removable	Removable
		Reversible
	Industry Standards	EIA-310-D
		EIA RS310-C
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	20 - M5
	Rack Type	2-Post
	Tools Included	No
	U Height	10U
	U Markings	No
Wallmountable	Yes	
Performance	Air Flow Rate	85 CFM
	Noise Level	36 dBA
	Weight Capacity (Stationary)	132.6 lb [60 kg]
Power	Input Current	180 mA
	Input Voltage	115V AC
Physical Characteristics	Color	Off White
	Enclosure Type	Steel
	Internal Depth	23.4 in [595 mm]
	Internal Height	17.6 in [448 mm]

	Internal Width	21.9 in [555 mm]
	Maximum Mounting Depth	17.7 in [450.9 mm]
	Minimum Mounting Depth	19.6 in [498 mm]
	Product Height	20 in [509 mm]
	Product Length	23.5 in [598 mm]
	Product Weight	38.5 lb [17.4 kg]
	Product Width	22 in [560 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	47.5 lb [21.5 kg]
What's in the Box	Included in Package	1 - 10U Server Rack Cabinet
		20 - M5 Screws
		20 - M5 Cage Nuts
		4 - Wall Anchor
		4 - Lag Screws
		2 - Keys
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.