

# USB-C to VGA Adapter with USB Power Delivery - 60 Watts - White

Product ID: CDP2VGAUCPW



This USB-C to VGA adapter connects a VGA display to your laptop or MacBook with USB Type-C. The USB-C adapter features USB Power Delivery, enabling you to power your laptop while outputting video to a using the same USB-C port. The adapter is also available in [black](#) (CDP2VGAUCP) so you can choose an adapter that matches the style of your laptop.

## Power and Video in One Port with USB Power Delivery

Smaller and lighter laptops are great for portability but you're left with fewer connectivity ports. This USB-C VGA adapter supports USB Power Delivery up to 60 watts and features an additional USB-C port, so you can charge your laptop using its USB-C power adapter, even while you output video. Many laptops like Dell XPS and MacBook Pro support charging through your USB-C port with USB Power Delivery, check your specifications to confirm compatibility.

## **Enjoy HD Picture Quality with Video Resolutions up to 2048 x 1260**

To ensure the quality of your video signal is maintained the USB-C dongle supports VGA resolutions up to 2048 x 1260 60Hz, including popular high-definition resolutions like 1080p and 720p.

## **Stylish Connectivity for Your MacBook or Any Laptop**

This USB Type-C adapter has an all-white housing and built-in USB-C cable designed to match your MacBook. The adapter is compatible with any device that supports USB-C DP Alt Mode, such as the 2018 iPad Pro.

The CDP2VGAUCPW is backed by a 3-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect to any VGA display while travelling
- Connect your BYOD laptop to a VGA display at work, school or home while charging your laptop
- Present on a large VGA display using your USB-C laptop

### Features

- Charge your laptop while connecting a VGA display using just one USB-C port, with USB Power Delivery
- Get crystal-clear picture quality with support for HD video resolutions up to 2048x1280 60Hz including 1080p
- Make the perfect connection, with a white USB-C adapter that exactly matches the cables for your MacBook

<b>Hardware</b>	Warranty	3 Years
	AV Input	USB Type-C
	AV Output	VGA
	Chipset ID	ITE - IT6516 VIA/VLI - VL100
<b>Performance</b>	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Supported Resolutions	1920 x 1200 @ 60Hz 1920 x 1080 1280 x 720 1680 x 1050 1600 x 900 1440 x 900 1360 x 768 1280 x 800 1280 x 768
		<i>Lower resolutions and refresh rates may also be supported</i>
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output 1 - USB-C (24 pin) USB Power Delivery only Female
<b>Special Notes / Requirements</b>	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter
<b>Power</b>	Power Delivery	60W
	Power Source	USB-Powered
<b>Environmental</b>	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	4 in [102 mm]
	Color	White
	Product Height	0.6 in [15 mm]
	Product Length	5.9 in [150 mm]
	Product Weight	0.8 oz [24 g]
	Product Width	1.3 in [33 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	0.2 lb [0.1 kg]

---

<b>What's in the Box</b>	Included in Package	1 - USB-C to VGA adapter
--------------------------	---------------------	--------------------------

---

Product appearance and specifications are subject to change without notice.