

# Dual Monitor USB-C Dock - 60W Power Delivery - 4K

Product ID: DKWG30DPPDU



This USB-C dock lets you transform your Windows 10 laptop into a full-sized workstation, connecting two external monitors (DisplayPort and HDMI®) or single 4K monitor.

## Power your dock and laptop with one adapter

With 60W Power Delivery, the docking station simultaneously powers and charges your laptop, while powering all devices connected to your laptop and the dock. A single adapter powers your dock and laptop.

## Dual-monitor video output

Create a dual-monitor setup by connecting:

- 1x HDMI display and 1x DisplayPort display at 1920 x 1200p @ 60Hz

The USB-C dock also lets you connect to a single high-resolution 4K monitor, with:

- 1x HDMI display or 1x DisplayPort display at 3840 x 2160p @ 30Hz

### **Ample connections**

The USB-C dock has four USB 3.0 ports (2x USB 3.0 and 2x USB 2.0 ports including a front-accessible fast charge-and-sync port) plus Gigabit Ethernet (with PXE Boot support) and headset connections.

### **Versatile setup**

The dock's small footprint fits into any workspace. It sits solidly in the supplied stand, or you can position it horizontally.

### **Wireless docking option, where supported**

The dock also supports WiGig® if your laptop supports it. With wireless docking, you dock and undock your laptop without having to connect and disconnect a cable, saving time. Note: USB Power Delivery is only supported when connected through USB-C, and is not supported with WiGig. For WiGig, the dock must be positioned vertically.

The DKWG30DPHPDU is backed by a StarTech.com 3-year warranty and free lifetime technical support

## Certifications, Reports and Compatibility



## Applications

- Power and charge your USB-C equipped laptop, using only the dock's power adapter (through USB-C only)
- Deploy in offices and business settings or create hot desk workstation
- An essential accessory for the latest USB-C equipped laptops such as the HP® Spectre x360, Dell XPS™ 15, 13, or 12, Dell Latitude™ laptops and 2-in-1s
- Also supports laptops with WiGig wireless docking, ideal for those who travel to and from the office

## Features

- Power and charge your laptop with support for USB Power Delivery (up to 60 watts) when connected through USB-C
- Supports dual monitors with 1920 x 1200p @ 60Hz resolution on each display (DisplayPort and HDMI), or a single 4K monitor 3840 x 2160p @ 30Hz
- Connect your peripherals with 4x USB-A ports (2x USB 3.0, 2x USB 2.0) including a front-panel fast-charge and sync port (supports USB Battery Charging Specification 1.2)
- Transform your USB-C enabled Windows 10 laptop into a full-sized workstation
- Compact design (8" x 4.8") sits either upright (in solid stand) or horizontal
- Gigabit Ethernet RJ45 port (with PXE Boot support) and Wake-on-LAN (WOL), 3.5 mm headset port
- Thunderbolt™ 3 port compatible (the dock connects to a Thunderbolt 3 port at 5Gbps and will support USB Power Delivery)
- Supports WiGig wireless docking

<b>Hardware</b>	Warranty	3 Years	
	4K Support	Yes	
	Bus Type	USB-C	
		WiGig	
	Chipset ID	Intel - W13100 Synaptics - VMM3330 VIA/VLI - VL812 C-Media - CM6533 Realtek - RTL8153	
	Displays Supported	2	
	Fast-Charge Port(s)	Yes	
	Industry Standards	USB Battery Charging Specification Rev. 1.2 IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE 802.11ad USB 3.0 - Backward compatible with USB 2.0 and 1.1	
<b>Performance</b>	Auto MDIX	Yes	
	Compatible Networks	10/100/1000 Mbps	
	Full Duplex Support	Yes	
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
	Maximum Digital Resolutions	USB-C host: 1920 x 1200p @ 60Hz (DisplayPort and HDMI - Dual Monitors) 3840 x 2160p @ 30Hz (DisplayPort - Single Monitor) 3840 x 2160p @ 30Hz (HDMI - Single Monitor) WiGig host:  1920 x 1200p @ 60Hz (DisplayPort and HDMI - Dual Monitors) 2560 x 1600p @ 60Hz (DisplayPort - Single Monitor) 2560 x 1440p @ 60Hz (HDMI - Single Monitor)	
	PXE	Yes	
	Type and Rate	USB 3.0 - 5 Gbit/s  USB 2.0 - 480 Mbit/s	
	UASP Support	Yes	
	<b>Connector(s)</b>	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female  1 - DisplayPort (20 pin) Female  1 - HDMI (19 pin) Female  1 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female  1 - USB Type-A (9 pin) USB 3.0 Female

		<p>2 - USB Type-A (4 pin) USB 2.0 Female</p> <p>1 - 3.5 mm Mini-Jack (4 Position) Female</p> <p>1 - RJ-45 Female</p>
<b>Software</b>	OS Compatibility	Windows® 10
<b>Special Notes / Requirements</b>	<b>Note</b>	<p>The dock can connect to a host laptop's USB-C port even if it doesn't support USB Power Delivery 2.0 and DP alt mode. However, without support for these two protocols, the dock will not pass power through to your host laptop or support video output.</p> <p>The dock's DisplayPort port only supports active DisplayPort video adapters.</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. USB 3.1 Gen 2 offers speeds up to 10Gbps.</p> <p>A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).</p> <p>Video output capabilities are dependent on the video card and hardware specifications of the host laptop it's connected to. Certain video cards have limited video support, and some monitors will also limit the available resolution.</p> <p>When connected to your host laptop through WiGig the dock only supports 2-channel audio (5 and 7-channel audio is not supported).</p> <p>HDCP content is not supported when connected in WiGig mode.</p> <p>USB Power Delivery is only supported when connected through USB-C, and is not supported when connected through WiGig.</p> <p>For WiGig mode, the dock must be positioned vertically.</p>
	System and Cable Requirements	<p>A USB-C equipped host laptop (the host USB-C port must support USB Power Delivery 2.0 in order to power and charge your laptop, it must also support DP alt mode to enable video output) or a WiGig (IEEE 802.11ad) equipped host laptop.</p>
<b>Indicators</b>	LED Indicators	<p>1 - Power</p> <p>1 - Status</p>
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	2 A
	Input Voltage	100 ~ 240 AC

	Output Current	5 A
	Output Voltage	20V DC
	Plug Type	N
	Power Consumption (In Watts)	100
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0~95% RH (Non-condensing)
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
<b>Physical Characteristics</b>	Color	Black & Silver
	Enclosure Type	Plastic
	Product Height	203 mm [8 in]
	Product Length	121 mm [4.8 in]
	Product Weight	655 g [23.1 oz]
	Product Width	52 mm [2 in]
<b>Packaging Information</b>	Shipping (Package) Weight	2 kg [4.4 lb]
<b>What's in the Box</b>	Included in Package	1 - laptop dock
		1 - stand
		1 - USB-C 3.3 ft [1016 mm] cable
		1 - universal power adapter
		2 - power cords (EU, UK)
		1 - instruction manual

Product appearance and specifications are subject to change without notice.