

Black 5.25in SATA Hard Drive Mobile Rack Drawer

Product ID: DRW110SATBK



This high quality Removable SATA Hard Drive Drawer/Mobile Rack delivers a convenient SATA hot-swap solution, allowing you to quickly swap Serial ATA hard drives in and out of a computer without having to open the computer case.

Simply install the (included) drive bay into a 5.25in drive bay on the host computer, then mount a 3.5in SATA HDD in the (removable) caddy. Connecting the SATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the installed SATA drive.

To maximize performance and utilize the full speed potential of your SATA III hard drives, this HDD Backplane supports SATA III for transfer speeds up to 6 Gbps when paired with a compatible controller.

A suitable solution for large volume drives, the HDD drawer supports SATA, SATA II, and SATA III-6Gbps hard drives allowing you to swap in large amounts of data in a matter of seconds. The mobile rack/backplane is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

The drive caddy features a rear panel ball bearing fan that helps keep the enclosed drive cool, in turn helping to optimize operation while preserving drive lifespan. To prevent damage to the hard drive(s) while being transferred in and out of the computer, the drive caddy features shock absorbers and rubber cushioning that help limit vibration/shock to the drive. This mobile rack is also compatible with DRW113-series SATA hard drive caddies.

A dependable, long-lasting storage solution, the drive drawer features highly durable construction, with a 3K insertion rating and is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Add additional hot-swap bays to a server or workstation computer
- Replace or upgrade old IDE backplane with a SATA backplane
- System builders who need to image many drives simultaneously and quickly
- Environments where drives need to be replaced/removed regularly, without external protection for the drives required after removal
- Be able to replace/remove individual drives from a storage array with minimal or no system down time

Features

- Fits a single SATA drive into a front accessible 5.25" bay
- Plastic construction for the drive caddy and bay
- Key lockable drive caddy
- Rubber shock absorbers
- 3,000+ insertion rating
- 40mm ball-bearing cooling fan
- Power LED indicator
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Supports 3.5" form factor SATA hard drives

| | | |
|-------------------------------------|-------------------------------|---|
| Hardware | Warranty | 2 Years |
| | Compatible Drive Types | SATA |
| | Drive Size | 3.5in |
| | Fan Bearing Type | Ball Bearing |
| | Fan(s) | Yes |
| | Fans | 1 - 40 mm |
| | Front Door Key Lock | Yes |
| | Number of Drives | 1 |
| Performance | Shock Protection | Yes |
| Connector(s) | Drive Connectors | 1 - SATA (7 pin, Data) Receptacle 1 - SATA Power (15 pin) Receptacle |
| | Host Connectors | 1 - LP4 (4 pin, Molex Large Drive Power) Male 1 - SATA (7 pin, Data) Plug |
| Software | OS Compatibility | OS independent; No software or drivers required |
| Special Notes / Requirements | Note | Note: Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated |
| | System and Cable Requirements | PC or Mac with a 5.25 Inch Drive Bay |
| Indicators | LED Indicators | 1 - Power (Green) |
| Physical Characteristics | Color | Black |
| | Enclosure Type | Plastic |
| | Product Height | 1.6 in [41 mm] |
| | Product Length | 8.7 in [220 mm] |
| | Product Weight | 18.7 oz [530 g] |
| | Product Width | 5.8 in [148 mm] |
| Packaging Information | Shipping (Package) Weight | 1.3 lb [0.6 kg] |
| What's in the Box | Included in Package | 1 - 3.5in Mobile Rack Caddy |
| | | 1 - 5.25in Mobile Rack Bay |
| | | 2 - Keys |
| | | 1 - Bag of mounting screws |
| | | 1 - Instruction Manual |

Product appearance and specifications are subject to change without notice.