

## Professional 5.25in Aluminum ATA Hard Drive Mobile Rack w/ 2x 40mm Fan

Product ID: DRW115ATABK



This high quality Removable ATA Hard Drive Drawer/Mobile Rack delivers a convenient ATA storage solution, allowing you to quickly swap ATA66/ATA100 and ATA133 hard drives in and out of a computer without having to open the computer case.

Simply install the (included) drive bay into a 5.25in drive bay on the host computer, then mount a 3.5in ATA HDD in the (removable) caddy. Connecting the ATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the installed ATA drive.

A practical, time-saving storage solution, the drive drawer/mobile rack features front panel LED indicators that continuously display the operating status of the installed drive.

The drive caddy features dual ball-bearing fans that help keep the enclosed drive cool, in turn helping to optimize operation while preserving drive lifespan. To prevent damage to the hard drive(s) while being transferred in and out of the computer, the drive caddy features shock absorbers and rubber cushioning that help limit vibration/shock to the drive.

A dependable, long-lasting storage solution, the drive drawer features highly durable construction, with a 7K insertion rating and is backed by StarTech.com's 2 year warranty.

### Certifications, Reports and Compatibility



### Applications

- Can be conveniently used as a mobile back up system
- Heavy duty model made out of aluminum is ideal for use in offices, enterprises, workstations, universities, government organizations or other environments with heavy work loads and usage
- For use in servers and storage subsystems
- Perfect for mission critical control computers where downtime must be minimized

### Features

- Can be mounted from the side or the bottom
- Two ball-bearing fans maintain optimum cooling and increased air flow
- Caddy is built with a key lock mechanism to prevent the hard drive from being accidentally removed while in operation
- 4 LED indicators continuously show operating status of the drive drawer
- The frame and caddy is constructed with aluminium for maximum durability
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate up to 133 MBytes/s
- Swap Manager Software allows the hard drive to be removed or replaced while the system is running

<b>Hardware</b>	Warranty	2 Years	
	Compatible Drive Types	IDE (ATA)	
	Drive Size	3.5in	
	Fan Bearing Type	Ball Bearing	
	Fans	2 - 40 mm	
	Front Door Key Lock	Yes	
<b>Performance</b>	Hot Swap Capability	Yes	
	Shock Protection	Yes	
<b>Connector(s)</b>	Connector Type(s)	1 - IDE (40 Pin, EIDE/PATA) Female 1 - IDE (40 Pin, EIDE/PATA) Male 1 - LP4 (4 pin; Molex-type Large Drive Power) Female 1 - LP4 (4 pin; Molex-type Large Drive Power) Male	
	<b>Special Notes / Requirements</b>	<b>Note</b> Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated	
	<b>Indicators</b>	LED Indicators	1 - Activity (Yellow) 1 - Fan Failure (Red) 1 - Power (Green) 1 - Temperature Warning (Green/Red)
		<b>Physical Characteristics</b>	Color
Enclosure Type			Aluminum
Product Height			1.6 in [41 mm]
Product Length	9.3 in [236 mm]		
Product Weight	34.6 oz [980 g]		
Product Width	5.7 in [146 mm]		
<b>Packaging Information</b>	Shipping (Package) Weight	2.4 lb [1.1 kg]	
<b>What's in the Box</b>	Included in Package	1 - Hard Drive Caddy 1 - 5.25in Bay 2 - Key 8 - Mounting Screws 1 - Software CD 1 - Instruction Manual	

Product appearance and specifications are subject to change without notice.