

Gigabit Ethernet over Coaxial Unmanaged Network Extender Kit - 2.4km

Product ID: EOC1110K



The EOC1110K Gigabit Ethernet over Coaxial Unmanaged LAN Extender Kit (2.4km) includes both end points, and allows you to span a 10/100/1000Mbps Ethernet network over extremely long distances (up to 2.4 km/1.5 mi) while still maintaining high-speed network connectivity.

The coax Ethernet extender allows you to run the connection over existing coaxial cable, with little to no modification required, making it a perfect solution for a broad range of applications, including connecting isolated user stations from the same or separate building, or overcoming infrastructure obstacles and distances (e.g. older stone/concrete architecture) where new wiring or wireless connectivity may be impossible.

The gigabit Ethernet over coax kit helps to eliminate expense by allowing CCD or CATV video and Ethernet network data to share the same coaxial cable without interference.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Extend an Ethernet network across an existing closed circuit camera network (over coax) without interrupting the analog TV signal
- Provide high-speed connectivity to a user or network segment that is in an isolated area of a large complex or in another building
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues at extreme distances
- Industrial applications include controlling CNC machinery, polling bar code scanner data, administering process control equipment, and other harsh environment applications
- Monitor and control medical equipment, security keypads/card scanners, point of sale equipment and remote sensor data, and various other healthcare related network communications
- Remote sensor monitoring for traffic flow management (air traffic control, expressway flow)

Features

- Plug-and-play design for simple installation; no configuration or software required
- Uses existing coaxial cable, RG-59, RG-6, RG-7, or RG-11
- Transmit up to 2.4 km (1.5 mi)
- Transparent TCP/IP Operations
- Auto-MDIX and Auto-negotiation 10/100/1000Base-T and Full or Half-Duplex on the Ethernet port
- Compliant with HCNA (ITU G.9954 – HPNA 3.1)
- Status LEDs for simple monitoring of the device and connection status

Hardware	Warranty	2 Years
	Industry Standards	HCNA (ITU G.9954 – HPNA 3.1) IEEE 802.3 10BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.3u 100BASE-TX
	Performance	
	Max Transfer Distance	2.4 km (1.5 mi)
	Maximum Data Transfer Rate	Up to 112Mbps @ 2,952 ft (900 m) Up to 64Mbps @ 1.5 mi (2.4 km) Speed/distance will vary depending on type/quality of line used (see manual for detailed chart)
	MTBF	57,000 Hours
	Transmission Power	0 dBm, 12~44MHz
Connector(s)	Local Unit Connectors	1 - RJ-45 Female 2 - Type F (RF Coax) Female
	Remote Unit Connectors	1 - RJ-45 Female 2 - Type F (RF Coax) Female
	Special Notes / Requirements	System and Cable Requirements
		75Ω (ohm) coaxial RG-59, RG-6, RG-7, or RG-11 cable is required
Indicators	LED Indicators	1 - Coax Link/Activity 1 - Coax Sync 1 - LAN Link/Activity 1 - Power
	Power	
	Center Tip Polarity	Positive
	Input Current	0.36A
	Input Voltage	110V-240V AC
	Output Current	1.6 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	4
	Power Source	2 AC Adapters Included
Environmental	Humidity	10~90% RH
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)

Physical Characteristics	Color	Black
	Product Height	1.1 in [29 mm]
	Product Length	3 in [77 mm]
	Product Weight	23.5 oz [667 g]
	Product Width	5.4 in [138 mm]
Packaging Information	Shipping (Package) Weight	3.4 lb [1.6 kg]
What's in the Box	Included in Package	1 - Local Unit
		1 - Remote Unit
		2 - Universal Power Adapters (NA/EU/UK) or AU in Austria
		1 - User Manual

Product appearance and specifications are subject to change without notice.