

# Gigabit Ethernet Fiber Media Converter Card Module with Open SFP Slot

Product ID: ET91000SFP2C



The ET91000SFP2C Open SFP Fiber Media Converter card module converts and extends a Gigabit Ethernet connection over fiber, using the Gigabit SFP of your choice.

A versatile solution for connecting an Ethernet (1000Base-T) network to remote network segments over a fiber backbone, the media converter features an open SFP slot that lets you choose the MSA-Compliant Gigabit SFP that best suits your fiber connection mode (single / multi-mode) and distance requirements (see our full line of [Gigabit transceivers](#) for compatible solutions).

Designed for applications where multiple chassis-powered media converters are required, this Gigabit media converter ships as a card module that can easily be installed into the 20 Slot, [2U Rackmount Chassis](#) (ETCHS2U). For standalone operation this Gigabit media converter can also be purchased as a standard [Open SFP Media Converter](#) (ET91000SFP2).

The fiber to Ethernet converter offers simple plug-and-play installation, while support for full-duplex operation and Jumbo Frame support provides efficient network operation.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Mount multiple media converter cards into a rack mount chassis
- Cost-effective way to extend/bridge networks using fiber cabling
- Provides connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether
- Perfect for secure connections required by government agencies where EMI is not acceptable
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues

### Features

- Media Converter card module designed for installation into the ETCHS2U Rackmount Chassis
- Open SFP slot supports MSA-Compliant Single / Multi-Mode Gigabit SFPs at varying distances
- Advanced features include Link-loss forwarding, remote monitor status, two frame lengths
- Supports full or half-duplex operation
- Easy to use and install
- Jumbo Frame support

<b>Hardware</b>	Warranty	2 Years
	Chipset ID	Marvell - 88E1111
	Industry Standards	IEEE 802.3ab 1000BASE-T
		IEEE 802.3u 100BASE-LX
		IEEE 802.3z 1000BASE-SX
PoE	No	
WDM	No	
<b>Performance</b>	Auto MDIX	Yes
	Fiber Operating Mode	Half/Full-Duplex
	Maximum Data Transfer Rate	1.25 Gbps
	MTBF	65, 000 Hours
<b>Connector(s)</b>	Local Unit Connectors	1 - RJ-45 Female 1 - SFP Slot Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Fiber data transfer speeds and distances are dependent on the SFP used (sold separately)
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1 A
	Input Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	< 8W
	Power Source	Not Included (not required for standard applications)
<b>Environmental</b>	Humidity	10~90% RH (Non-Condensing)
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Product Height	0.8 in [21 mm]
	Product Length	5.6 in [142 mm]
	Product Weight	3.9 oz [110 g]
	Product Width	2.9 in [74 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	6.5 oz [184 g]
<b>What's in the Box</b>	Included in Package	1 - Fiber Media Converter
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.