

## Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - ST/SC - 2 m

Product ID: FIBSTSC2



The FIBSTSC2 2-meter (6.6ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one ST (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This ST-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our ST-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

### Certifications, Reports and Compatibility



### Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication
- Used by long distance networks with mission critical data

### Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

|                                 |                            |  |
|---------------------------------|----------------------------|--|
| <b>Hardware</b>                 | Warranty                   | Lifetime   |
|                                 | Fiber Size                 | 62.5/125   |
|                                 | Fire Rating                | LSZH Rated (Low Smoke Zero Halogen)                        |
| <b>Performance</b>              | Cable Rating               | 1Gbps / 10Gbps   |
|                                 | Fiber Classification       | OM1  |
|                                 | Maximum Data Transfer Rate | 10Gbps   |
|                                 | Type                       | Multi Mode   |
| <b>Connector(s)</b>             | Connector A                | 1 - Fiber Optic ST Duplex Male                             |
|                                 | Connector B                | 1 - Fiber Optic SC Duplex Male                             |
| <b>Physical Characteristics</b> | Cable Length               | 6.6 ft [2 m]   |
|                                 | Color                      | Orange   |
|                                 | Product Length             | 6.6 ft [2 m]   |
| <b>Packaging Information</b>    | Shipping (Package) Weight  | 0.1 lb [0.1 kg]  |
| <b>What's in the Box</b>        | Included in Package        | 1 - 2m Multimode 62.5/125 Duplex Fiber Patch Cable ST - SC |

Product appearance and specifications are subject to change without notice.