

Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - ST/SC - 2 m

Product ID: FIBSTSC2



The FIBSTSC2 2-meter (6.6ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one ST (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This ST-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our ST-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Certifications, Reports and Compatibility



Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication
- Used by long distance networks with mission critical data

Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Hardware	Warranty	Lifetime
	Fiber Size	62.5/125
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Performance	Cable Rating	1Gbps / 10Gbps
	Fiber Classification	OM1
	Fiber Type	Multi Mode
	Maximum Data Transfer Rate	10Gbps
Connector(s)	Connector A	1 - Fiber Optic ST Duplex Male
	Connector B	1 - Fiber Optic SC Duplex Male
Physical Characteristics	Cable Length	6.6 ft [2 m]
	Color	Orange
	Product Length	6.6 ft [2 m]
Packaging Information	Shipping (Package) Weight	0.1 lb [0.1 kg]
What's in the Box	Included in Package	1 - 2m Multimode 62.5/125 Duplex Fiber Patch Cable ST - SC

Product appearance and specifications are subject to change without notice.