

Gigabit Ethernet to SC Fiber Media Converter - 1000Base-SX - Multimode 550 m

Product ID: MCMGBSCMM055



This fiber media converter extends a Gigabit Ethernet (1000Mbps) network up to 550 m over multimode fiber, on 1000BASE-SX networks.

Extend your GbE network cost-effectively

The fiber media converter offers a cost-effective way to transparently convert copper to fiber, or fiber to copper, for connecting remote sub-networks to larger fiber-optic networks. Providing both SC fiber and RJ45 Ethernet ports, it integrates easily into a wide range of Gigabit Ethernet network infrastructures. The RJ45 port supports triple-speed (10/100/1000 BASE-T) auto-negotiation.

Reliable and scalable network connectivity

Supporting a maximum multimode fiber-optic cable distance of 550 meters (0.34 miles), the media converter delivers a simple and reliable solution for connecting Gigabit Ethernet networks to remote locations over multimode fiber, while ensuring solid network performance. It provides optimum network scalability for connecting two or more Ethernet network nodes, for instance, connecting two buildings on the same campus or facility. The media converter also offers high-speed bandwidth to meet the increasing demands of large-scale workgroups that require expansion of a Gigabit Ethernet network.

The MCMGBSCMM055 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Extend an Ethernet connection by up to 550 m (0.34 miles) over a fiber backbone
- Create an economical Ethernet-fiber/copper-fiber link for connecting remote sub-networks to larger fiber-optic networks/backbones
- Converts Ethernet to fiber, and fiber to copper to provide a cost-effective networking solution

Features

- Converts and extends a Gigabit Ethernet fiber (1000Mbps) network over multimode fiber on 1000BASE-SX networks
- Provides a cost-effective Ethernet to fiber/copper to fiber link
- Supports a maximum distance of 550 m over multimode fiber-optic cable (SC connection)
- Compact design and wall mountable
- Non-blocking full wire-speed forwarding rate
- Provides DIP switch supporting Link Fault Pass-through function
- LED Indicators for simple Ethernet/fiber network link monitoring
- 850 nm wavelength
- Supports IEEE 802.1q Tag VLAN pass-through

Hardware	Warranty	2 Years
	Industry Standards	IEEE 802.3z 1000BASE-SX
		IEEE 802.3ab 1000BASE-T
		IEEE 802.3u 100BASE-TX
		IEEE 802.3x full-duplex flow control
	IEEE 802.3 10BASE-T	
	IEEE 802.1q VLAN pass through	
	PoE	No
	WDM	No
Performance	Auto MDIX	Yes
	Fiber Operating Mode	Full-Duplex
	Jumbo Frame Support	9K max.
	Max Transfer Distance	550 m (1804 ft)
	Maximum Data Transfer Rate	1000 Mbps (1 Gbps)
	MTBF	> 50,000 hours at 25°C
	Supports a maximum distance of 550 m over MM fiber-optic cable (SC connection), and 100m over copper (RJ45 connection)	10/100/1000 Mbps Data Transfer Rate Fiber: 1000 Mbps ESD Surge Protection: 1KV. Contact discharge - 4KV. Air discharge - 8KV
	Data Transfer Rate Copper	
	Switching Architecture	Store-and-Forward
	Type	Multi Mode
	Wavelength	850nm
Connector(s)	Local Unit Connectors	1 - RJ-45 Female
	Remote Unit Connectors	1 - Fiber Optic SC Duplex Female
Indicators	LED Indicators	1 - 1000 Link: ON - Valid Gigabit Link
		1 - FX Link/Activity
		1 - Power
		1 - TP Link/Activity
Power	Center Tip Polarity	Positive
	Input Current	0.5 A
	Input Voltage	100 ~ 240 AC
	Output Current	2.6 A

	Output Voltage	5 DC
	Plug Type	N
	Power Consumption (In Watts)	5
	Power Source	AC Adapter Included
Environmental	Humidity	5 ~ 90% RH
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Color	Brown
	Enclosure Type	Steel
	Product Height	1 in [26 mm]
	Product Length	2.8 in [70 mm]
	Product Weight	7.1 oz [200 g]
	Product Width	3.8 in [97 mm]
Packaging Information	Shipping (Package) Weight	19.9 oz [564 g]
What's in the Box	Included in Package	1 - media converter 1 - universal power adapter (NA/JP, UK, EU, ANZ) 1 - quick-start guide

Product appearance and specifications are subject to change without notice.