

# Cisco QSFP-40G-SR4 Compatible QSFP+ Transceiver Module - 40GBASE-SR4

Product ID: QSFP40GSR4ST



The QSFP40GSR4ST is a Cisco QSFP-40G-SR4 compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco™ brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBASE-SR4 compliant networks, with a maximum distance of up to 150 m (492 ft).

## Technical Specifications:

- **Wavelength:** 850nm
- **Maximum Data Transfer Rate:** 40 Gbps
- **Type:** Multi Mode Fiber
- **Connection Type:** MPO Connector
- **Maximum Transfer Distance:** 150 m (492 ft)
- **MTBF:** 1,649,326 hours
- **Power Consumption:** Less than 0.7 Watts
- **Digital Diagnostics Monitoring (DDM):** Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

### **StarTech.com SFPs**

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

### Certifications, Reports and Compatibility



### Applications

- Replacing defective or damaged SFP+ modules in Cisco switches and routers
- Expand your network to remote segments

### Features

- 100% compatibility with Cisco QSFP-40G-SR4 guaranteed
- StarTech.com SFP modules are backed by a lifetime warranty
- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption of less than 0.7 W
- Hot-swappable with fiber-optic modules

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	Cisco
	Industry Standards	IEEE 802.3ba 40GBASE-SR4
<b>Performance</b>	Compatible Networks	40 Gbps
	DDM	Yes
	Fiber Operating Mode	Full-Duplex
	Max Transfer Distance	150 m (492 ft)
	Maximum Data Transfer Rate	40 Gbps
	MTBF	1,649,326 hours
	Type	Multi Mode
	Wavelength	850nm
<b>Connector(s)</b>	Local Unit Connectors	1 - MPO Female
<b>Special Notes / Requirements</b>	<b>Note</b>	For use in 40 Gigabit fiber networking equipment and media converters
	System and Cable Requirements	MSA or Cisco compliant QSFP port
<b>Power</b>	Power Consumption (In Watts)	< 0.7 W
<b>Environmental</b>	Humidity	5~95% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 85°C (-40°F to 185°F)
<b>Physical Characteristics</b>	Color	Silver
	Enclosure Type	Aluminum
	Product Height	0.5 in [13 mm]
	Product Length	2.8 in [72 mm]
	Product Weight	1.1 oz [32 g]
	Product Width	0.7 in [18.4 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	3.4 oz [95 g]
<b>What's in the Box</b>	Included in Package	1 - QSFP+ transceiver

Product appearance and specifications are subject to change without notice.