

MSA Compliant QSFP+ Direct-Attach Twinax Cable - 2 m (6.6 ft)

Product ID: QSFPM2M



The QSFPM2M is an MSA compliant direct-attach copper QSFP+ cable that's designed, programmed and tested to work in 40G network deployments. It delivers dependable 40 GbE connectivity over copper cabling, which is a cost-effective alternative to fiber-optic cable setups.

This passive Twinax cable supports 40 Gigabit Ethernet applications connected through QSFP+ (Mini-GBIC) ports. The cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

At 2 meters long and designed for high-speed performance, this copper QSFP+ cable is ideal for medium-distance applications such as across-rack network switch or server connections.

StarTech.com SFP Cables

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Use in 40Gb Ethernet and 56Gb/s Infiniband applications
- Point-to-point in-rack and across rack network switch/server connections (Storage Area Networks (SAN), Network Attached Storage (NAS), Storage Servers, etc.)

Features

- Delivers reliable 40Gbps connections for 40GBase-T compliant networks
- StarTech.com SFP cables are backed by a lifetime warranty
- Uses a cost-effective cabling alternative to fiber-optic setups
- Meets or exceeds OEM specifications and MSA (Multi-Source Agreement) industry standards
- Low power consumption of less than 0.1 W
- Hot-swappable

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Compatible Brand	MSA Compliant
Performance	Compatible Networks	40 Gbps
	Impedance	100 Ohm
Connector(s)	Connector A	1 - QSFP+ Latching Plug
	Connector B	1 - QSFP+ Latching Plug
Power	Power Consumption (In Watts)	< 0.1 W (per end)
Physical Characteristics	Cable Length	6.6 ft [2 m]
	Color	Black
Packaging Information	Package Height	0.4 in [11 mm]
	Package Length	13 in [33 cm]
	Package Quantity	1
	Package Width	10 in [25.5 cm]
	Shipping (Package) Weight	6.7 oz [190 g]
What's in the Box	Included in Package	1 - 2m QSFP+ 40-Gigabit Ethernet (40GbE) Passive Copper Twinax Cable
	Product Height	0.4 in [1 cm]
	Product Length	6.6 ft [2 m]
	Product Width	0.7 in [18 mm]
	Weight of Product	6.2 oz [175 g]

Product appearance and specifications are subject to change without notice.