

2 Port VGA Video Splitter - 250 MHz

Product ID: ST122LEU



The ST122LEU 2 Port VGA Video Splitter allows a single VGA source to display VGA video onto two monitors simultaneously. Perfect for classrooms, tradeshow, or in-store displays where high quality video on several monitors is needed. The simple plug and play operation makes setup quick and easy so you can be up and running in minutes.

The ST122LEU supports displays with up to 250 MHz of bandwidth, providing brilliant resolutions up to 1920x1440. A built-in booster circuit lets you situate your displays up to 210 ft away from your source.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Male to Female VGA extension cable required (MXT101HQ)

Certifications, Reports and Compatibility



Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Supports resolutions up to 1920x1440
- Maximum cable distance 210 feet (65m)
- Supports Cascading up to 3 levels
- 250 MHz video bandwidth
- Compatible with VGA, SVGA and Multisync monitors

	Warranty	2 Years
Hardware	Ports	2
Performance	Bandwidth	250 MHz
	General Specifications	Male to Female VGA extension cable required (MXT101HQ)
	Maximum Analog Resolutions	1920x1440
	Maximum Cable Length	65 m [213.2 ft]
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male 1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	2 - VGA (15 pin, High Density D-Sub) Female
Power	Center Tip Polarity	Positive
	Input Current	0.5
	Output Current	0.5 A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	4.5
	Power Source	AC Adapter Included
Environmental	Humidity	0~90% RH, non-condensing
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	25.9 mm [1 in]
	Product Length	65 mm [2.6 in]
	Product Weight	221 g [7.8 oz]
	Product Width	131.1 mm [5.2 in]
Packaging Information	Shipping (Package) Weight	0.8 kg [1.9 lb]
What's in the Box	Included in Package	1 - 2 Port VGA Splitter 1 - Power Adapter 1 - User Manual

Product appearance and specifications are subject to change without notice.