


# Dual Port PCI Express (PCIe x4) Gigabit Ethernet Server Adapter Network Card - Intel i350 NIC

Product ID: ST2000SPEXI



The ST2000SPEXI PCI Express Dual Port Gigabit Network Card lets you add two gigabit Ethernet ports to a desktop computer through a single, four-lane (x4 or higher) PCI Express slot. Each port is fully compatible with IEEE 802.3/4/ab standards, for 10/100/1000 Mbps auto-negotiation.

This 2-port GbE network card is based on the high-performance Intel® I350 chipset, which offers several advanced driver options including IEEE 802.3ad link aggregation / teaming support, enabling you to add additional bandwidth to your system. Support for Jumbo Frames, full-duplex operation and 802.1q VLAN tagging also aid in creating an efficient network configuration.

Also useful for virtualization applications (check your VM software for chipset compatibility) or setting up a dual-homed host configuration, this dual-port network card lets you accommodate several complex network scenarios, to meet your business needs. For added versatility, the controller card is equipped with a standard profile bracket and includes a low-profile/half-height bracket for installation in small form-factor computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Ideal for VM environments with multiple operating systems, requiring shared or dedicated NICs
- Provide redundant connectivity to ensure an uninterrupted network connection
- Configure a dual-homed proxy or gateway system for an added layer of security
- Specially designed for desktop PC clients, servers, and workstations with few PCI Express slots available

### Features

- Two 10/100/1000Mbps compatible RJ-45 Ethernet ports
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE802.3ad (link aggregation) and supports IEEE 802.1Q VLAN tagging
- Jumbo Frame support up to 9k bytes
- Teaming Support
- Supports Checksum Offload (IP, TCP, UDP), Transmit Segmentation Offload (TCP, UDP) and Large send Offload
- Wake-on-LAN / Remote Wake-up support
- Configured with standard profile bracket, low profile/half-height bracket included
- Supports Intel® Virtualization Technology (VT-c, VMDq, SR-IOV)
- Four-lane (x4) PCI Express compatible with x4, x8 and x16 PCIe slots
- Compatible with PCI Express Base Specification 2.1 (backward compatible with 1.0a/1.1)

<b>Hardware</b>	Warranty	2 Years
	Bus Type	PCI Express
	Card Type	Standard Profile (LP bracket incl.)
	Chipset ID	Intel - I350-AM2
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab PCI Express Base Specification 2.1
	Interface	RJ45 (Gigabit Ethernet)
	Port Style	Integrated on Card
	Ports	2
<b>Performance</b>	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Jumbo Frame Support	9K max.
	Maximum Data Transfer Rate	2000 Mbps (full-duplex), 1000 Mbps (half-duplex)
	Promiscuous Mode	Yes
	Supported Protocols	IEEE 802.3ad (link aggregation), IEEE 1588 (time sync) / 802.1AS, IEEE 802.1q (VLAN tagging)
<b>Connector(s)</b>	Connector Type(s)	1 - PCI Express x4 Male
	External Ports	2 - RJ-45 Female
<b>Software</b>	OS Compatibility	Windows® 7, 8, 8.1, 10 Windows Server® 2008 R2, 2012, 2012 R2, 2016 Linux 2.4.x to 4.11.x <i>LTS versions only</i>
<b>Special Notes / Requirements</b>	System and Cable Requirements	Available PCI Express x4 or higher (x8, x16) slot
<b>Indicators</b>	LED Indicators	2 - 10/100/1000 Mbps Indicator 2 - Link / Activity
<b>Environmental</b>	Humidity	5~85% RH
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Product Height	4.8 in [121 mm]
	Product Length	2.6 in [67 mm]
	Product Weight	2.8 oz [80 g]

	Product Width	0.7 in [19 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	5.8 oz [165 g]
<b>What's in the Box</b>	Included in Package	1 - 2 Port Network Card 1 - Low Profile Bracket 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.