

6 ft 3-in-1 PS/2 KVM Cable

Product ID: SVPS23N1_6



The SVPS23N1_6 6ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and reliable connections.

Our universal PS/2 KVM switch cables are designed to prevent tangles and keep your workspace neat, while delivering excellent performance with your StarTech.com or other KVM switch.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

Triplite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

Features

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite core on video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

Connector(s)	Warranty	Lifetime
	Connector A	1 - VGA (15 pin, High Density D-Sub) Male 2 - PS/2 (6 pin, Mini-DIN) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female 2 - PS/2 (6 pin, Mini-DIN) Male
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Length	6 ft [1.8 m]
	Product Weight	13.1 oz [369.7 g]
Packaging Information	Shipping (Package) Weight	13.3 oz [376.7 g]
What's in the Box	Included in Package	1 - 6 Ft. PS/2 Style 3-in-1 KVM Switch Cable 1 - DB15 male/male gender changer (GC15HSM) 1 - metal part of thumbscrew must be 1.17in(3cm) 1 - THUMBSCREWS MUST BE 1.93 inches long (4.9cm) THUMBSCREWS MUST BE 1.93in(4.9cm)

Product appearance and specifications are subject to change without notice.