

2m Mini USB Cable - A to Down Angle Mini B

Product ID: USBAMB2MD



The USBAMB2MD 2m USB to Down Angle Mini USB Cable provides a high quality connection between your Mini USB 2.0 mobile devices (smartphones, GPS, digital cameras, portable hard drives, etc.) and your PC or Mac® computer, for everyday tasks such as charging, data synchronization or file transfers.

The down-angled Mini USB connector allows you to access your Mini USB devices, while keeping the cable out of the way, and stress away from the port.

Designed and constructed for maximum durability, this high quality USB to Mini USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a [2m USB to Up Angle Mini USB Cable \(USBAUB2MU\)](#), which provides the same convenience as this down-angled cable, but allows you to connect to your Mini USB device from the opposite direction.

Certifications, Reports and Compatibility



Applications

- Transfer data and provide power while charging your Mini USB device, without the cable getting in the way

Features

- 1x USB 'A' male connector
- 1x Down Angle USB Mini-B male connector
- Supports high-speed data transfer rates of up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief
- Offers 2m in cable length

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Mini-B (5 pin) Male
Physical Characteristics	Cable Length	6.6 ft [2 m]
	Color	Black
	Connector Style	Straight to Down Angle
	Product Height	0.8 in [20 mm]
	Product Length	6.6 ft [2 m]
	Product Weight	1.5 oz [43 g]
	Product Width	0.6 in [16 mm]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	1.7 oz [48 g]
What's in the Box	Included in Package	1 - 2m Mini USB Cable - A to Down Angle Mini B

Product appearance and specifications are subject to change without notice.