

1m Micro USB Cable - A to Down Angle Micro B

Product ID: USBAUB1MD



The USBAUB1MD 1m USB to Down Angle Micro USB Cable provides a high quality connection between your Micro USB 2.0 mobile devices (smartphones, digital cameras, Tablet PC devices, portable hard drives, etc.) and your PC or Mac® computer, for everyday tasks such as charging, data synchronization or file transfers.

The down-angled Micro USB connector allows you to access your mobile Micro USB devices, while keeping the cable out of the way, and stress away from the port.

Designed and constructed for maximum durability, this high quality USB to Micro USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a [1m USB to Up Angle Micro USB Cable](#) (USBAUB1MU), which provides the same convenience as this down-angled cable, but allows you to connect to your Micro USB device from the opposite direction.

Certifications, Reports and Compatibility



Applications

- Transfer data and provide power while charging your Micro USB device, without the cable getting in the way

Features

- 1x USB 'A' male connector
- 1x Down Angle USB Micro-B male connector
- Supports high-speed data transfer rates of up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Micro-B (5 pin) Male
Physical Characteristics	Cable Length	3.3 ft [1 m]
	Color	Black
	Connector Style	Straight to Down Angle
	Product Height	0.7 in [19 mm]
	Product Length	3.3 ft [1 m]
	Product Weight	1 oz [27 g]
	Product Width	0.6 in [15 mm]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	1.2 oz [33 g]
What's in the Box	Included in Package	1 - 1m Micro USB Cable - A to Down Angle Micro B

Product appearance and specifications are subject to change without notice.